



Hekto, PC Based Audiometer

The Hekto audiometer is a PC based Screening Audiometer.

It is extremely portable but with a heavy duty design. It is used in conjunction with the supplied ARKO software to provide an easy to use, user friendly audiometer.

Simply connect the Hekto PC Audiometer to any Windows OS PC with the supplied USB cable, install the ARKO software, and you will be up and testing in no time at all.

All test results can be stored in the ARKO software database located on the PC's drive, or printed from any printer connect to the PC.

During the test, the audiometer controls can be operated either via the PC Mouse, Keyboard, or used in the fully automatic mode.



70 Lewis Rd Hoddles Creek, Vic. 3139



PO Box 212, Woori Yallock, Vic. 3139



0493 139 141



@sales@prismat.com.au



www.prismat.com.au

The Hekto Screening Audiometer is more than just a basic Screening Audiometer.

It features:

- Pure Tone Audiometry,
- Free Field Audiometry, and
- Automatic Hughson Westlake Testing.

Hekto PC Based Screening Audiometer Features and specifications:	
<i>Air Conduction Frequencies:</i>	125 to 8000 Hz
<i>dB Range</i>	-10dB to 120 dB HL (@ 1KHz)
<i>Channels</i>	2
<i>Weight</i>	250 grams
<i>Dimensions</i>	170mm x 95mm x 25mm
<i>Masking</i>	White & Narrow Band Noise
<i>Automatic test protocol</i>	Hughson Westlake
<i>Maximum Comfort Level Testing (MCL)</i>	Yes
<i>Uncomfortable Level Testing (UCL)</i>	Yes

Other Hekto Audiometers in this range:

Hekto Diagnostic:

2 Channel Air & Bone Conduction, Masking, PTA, Speech Audiometry.

Hekto Tinnitus Assessor: ABLB, SISI, Tone Decay, Bekesy Audiometry, High Frequency Audiometry, Tinnitus Assessment.